

Standards

EN140: 1998 Mask Body
EN143: 2000+A1: 2006 P3 RD
CE 2797

Efficiency

P3 >99,95% for 0,3 µ particulate

Weight

Mask + Filter: net (S/M) 132 g; (M/L) 140 g
gross (S/M) 187 g; (M/L) 195 g
Filter: net 19 g each; both net 38 g, gross 61 g

Shelf Live


5 years (mask & filters) See storage conditions on Instructions for Use.
Filters are re-usable and changeable.

Material

- **Mask:** Medical grade TPE Conforms to ISO 10993-10: 2010 for irritations. Mask body latex and silicone free, odour free. Valve Body in Nylon, Inhalation/Exhalation diaphragm in Silicone. 4 point adjustable elasticated head and neck strap with comfort pad in TPE.
- **Filters:** Mechanical type multi-layer HESPA Synthetic media with TPE flexible overmolded / encapsulated. Glued additional carbon activated impregnated media.

Production

United Kingdom, Italy, Romania
100% of filters NaCl Tested



Encapsulation (patented technology)

645 mm; lenght of actual media in each filter

Code	Description	Quantity
SPR337 (S/M) SPR502(M/L)	Elipse Half Mask complete with P3 Nuisance Odour filters	10 pcs. per box
SPR336	Elipse P3 Nuisance Odour replacement filters	10 sets of 2 pcs. per box
SPM001	Elipse Dust Mask Carry Case (Belt holder)	10 sets per box
SPM414	Portacount Face Fit Kit adaptor	10 sets per box

Applications - dust, mist, fumes, ozone and smells



Welding and Grinding

Metal Fumes, Dust,
Ozone: up to 10 x WEL



Construction

Silica Dust, Abestos, Concrete
Dust, Stone Dust, Aggregate
Dust, Wood Dust, Cement
Dust, Mold



Mining

Coal Dust, Silica Dust



Manufacturing

Glass Fibres, Composite
Fibres, Lead Fumes



Food

Poultry, Powders (Dairy),
Spices, Grain Dust



Pharmaceutical

Powders, Viruses